SIEMENS

April 2012

5WG1 117-2AB12

Bus Coupling Unit (BTM) UP117/12

Product – and Applications Description



Bus Coupling Units (BTM) UP 117 provide the connection to the bus for DELTA switches and wall box mounted control devices with Bus Transceiver Interface (BTI).

The Bus Coupling Unit (BTM) UP 117/12 comes with a mounting frame for DIN/VDE type wall boxes.

Application Programs

The Bus Coupling Unit (BTM) does not require an application program.

Example of Operation




figure 1: Example of operation

Installation Instructions

• The device can be used for permanent installation in dry interior rooms, for mounting in wall boxes.

WARNING

- The device must be mounted and commissioned by an authorized electrician.
- The prevailing safety rules must be heeded.
- The device must not be opened.
- For planning and construction of electrical installations, the relevant guidelines, regulations and standards of the respective country are to be considered.

April 2012

Bus Coupling Unit (BTM) UP117/12

5WG1 117-2AB12

Technical Data

Power supply

- Input voltage
- Bus: DC 24V (DC 21...30V)

Output voltage and current via BTI

- DC 5V, 10mA
- DC 20V, 25mA

Operator elements

The device has no operator elements.

Display elements

The device has no display elements.

Connections

- Bus line : screwless bus connection block (red-black) 0.6...0.8 mm Ø single core
- 10-pin socket (BTI): for connection of DELTA switches and wall box mounted control devices with BTI plug

Physical specifications

- housing: plastic
- dimensions (L x W x D): 45,5 x 50 x 17,9 mm
- weight: approx. 45 g
- installation: mounted with mounting frame on DIN/VDE type wall boxes

Electrical safety

- degree of pollution (according to IEC 60664-1): 2
- protection (according to EN 60529): IP 20
- overvoltage class (according to IEC 60664-1): III
- bus: safety extra low voltage SELV DC 24 V
- the device complies with EN 50428

Electromagnetic compatibility

complies with EN 50428, EN 61000-6-2, and EN 50371

Environmental specifications

- climatic conditions: EN 50090-2-2
- ambient temperature operating: 5 ... + 45 °C
- ambient temperature non-op.: 25 ... + 70 ° C
- relative humidity (non-condensing): 5 % to 93 %

Markings

EIB, KNX

CE mark

complies with the EMC regulations (residential and functional buildings), and low voltage regulations Location and Function of the Display and Operator Elements




figure 2: Location and Function of the Display and Operator Elements

- A1 Bus Transceiver Interface (BTI) socket for connecting an application unit with BTI plug
- A2 Slots for attaching the Bus Coupling Unit (BTM) to wall boxes
- A3 Slots for mounting application unit with guide and mounting clamps
- A4 Thread for mounting screws (for additional support, e.g. for securing the application unit against theft)
- A5 Type plate
- A6 Bus connection block for single core conductors with Ø 0.6 ... 0.8 mm
- A7 earthing plate

Technical-Manual

Update: http://www.siemens.com/gamma

© Siemens AG 2012 Subject to change without further notice

Technik-Handbuch

Update: http://www.siemens.com/gamma

Bus Coupling Unit (BTM) UP117/12

Mounting and Wiring

General description

The connection to the bus line is established via bus connection block 193 (screwless plug-in terminals for single core conductors). The application unit is slipped onto the bus coupling unit (BTM) via guide and mounting clamps and, depending on the device type, fastened with screws.

Note

The Bus Coupling Unit (BTM) UP 117 must be mounted with the Bus Transceiver Interface (BTI) situated at the bottom (see Figure 2). Thus, the application unit will be oriented properly when slid onto the BTI. Use bus devices with mounting screws only to achieve a permanently stable contact at the BTI.

Mounting




figure 3: mounting

- B1 wall box (60 mm Ø, according to DIN 49073)
- B2 mounting slots
- B3 Bus Transceiver Interface (BTI)
- B4 Bus coupling unit (BTM) UP 117
- B5 mounting screws

Slipping off/on bus connection blocks

The bus connection block (C2) is situated on the back of the bus coupling unit (BTM) (C1).

It consists of two components (C2.1 and C2.2) with four terminal contacts each. Take care not to damage the two test sockets (C2.3) by accidentally connecting them to the bus cable or with the screw driver (e.g. when attempting to unplug the bus connection block).

Slipping off bus connection blocks

- Carefully put the screw driver to the wire insertion slit of the bus connection block's grey component (C2.2) and
- pull the bus connection block (C2) from the bus coupling unit (BTM) (C1).

Note

Don't try to remove the bus connection block from the bottom side. There is a risk of shorting-out the device!




figure 4: Slipping off/on bus connection blocks (figure 3)

Slipping on bus connection blocks

- Slip the bus connection block (C2) onto the guide slot of the BTM (C1) and
- press the bus connection

Connecting bus cables

- The bus connection block (D1) can be used with single core conductors Ø 0.6...0.8 mm.
- Remove approx. 5 mm of insulation from the conductor (D2) and plug it into the bus connection block (D1) (red = +, grey = -)

Disconnecting bus cables

- Unplug the bus connection block (D1) and remove the bus cable conductor (D2) while simultaneously wiggling it.



figure 5: Connecting/Disconnecting bus cables

...gui e et inte uniting


April 2012

5WG1 117-2AB12

Bus Coupling Unit (BTM) UP117/12

Dimension Diagram

Dimensions in mm



General Notes

- The operating instructions must be handed over to the client.
- Any faulty device is to be sent together with a return delivery note of the local Siemens office.
- For any technical questions, please consult:

+49 (911) 895-7222

島 +49 (911) 895-7223

 \boxtimes support.automation@siemens.com www.siemens.com/automation/support-request

Update: http://www.siemens.com/gamma

$\ensuremath{\textcircled{C}}$ Siemens AG 2012 Subject to change without further notice

Siemens AG Infrastructure and Cities Sector, Building Technologies Control Products and Systems P.O. Box 10 09 53, D-93009 Regensburg

5WG1 117-2AB12