
April 2003

Load Switch N 512 8 x 230 V AC / 16 A 5WG1 512-1AB01

Product and Applications Description



The load switch N 512 is a N-system DIN-rail mounted device. Via its eight outputs it can switch eight separate groups of electric devices. The power supply of the load switch N 512 is provided by the bus (i.e., it requires no additional power supply).

The outputs may be operated manually via slide switches. These switches also show the actual switching state (when switching manually as well as when switching via the bus). Each of the outputs (relays) can be assigned various tasks depending on the application program used, i.e. the load switch N 512 consists of the device (hardware) and its application programs (software).

The load switch N 512 can handle different tasks; e.g. non-delayed on and off switching.


With the ETS (EIB Tool Software) the application program is selected, its parameters and addresses are assigned appropriately, and downloaded to the load switch N 512.

Application Programs

20 A8 Binary with Status 900701

- · relations can be set
- initial value of the relation at bus voltage recurrence
- on/off -delay mode available
- operation mode of the relay: NO/NC
- operation mode: normal/time switch
- characteristic in case of bus voltage failure/bus voltage recurrence can be set in parameter list

Example of Operation



Installation Instructions

 The device may be used for permanent interior installations in dry locations within distribution boards or small casings with DIN rail EN 60715-TH35-7,5.



WARNING

- The device must be mounted and commissioned by an authorised electrician.
- A safety disconnection of the device must be possible. Especially if the device is connected to different phases.
- Free DIN rail areas with sticked-in data rail must be covered with covers, order no. 5WG1 192-8AA01.
- The prevailing safety rules must be heeded.
- The device must not be opened.
- For planning and construction of electric installations, the relevant guidelines, regulations and standards of the respective country are to be considered.

Subject to change without prior notice

Technical Product Information

April 2003

Load Switch N 512 8 x 230 V AC / 16 A 5WG1 512-1AB01

Technical Specifications

Power supply

via bus line

Outputs

- number: 8 (bistable relays, volt free contacts)
- rated voltage: AC 230 V, 50 ... 60 Hz
- rated current: 16 A resistive load AC1
- switching current at AC 230 V: 0,01...16 A resistive load
- switching characteristic: set in parameter list according to application program

Control elements

- 1 learning button: for switching between normal operating mode and addressing mode
- 8 slide switches for manual operation

Display elements

- 1 red LED:
 - for monitoring bus voltage and displaying mode, selected with the learning button
- 8 slide switches providing switching state information

Connections

- load circuit, physical: strip insulation for 9 ... 10 mm permissible conductor types/cross sections:
 - 0,5 ... 4 mm² single core
 - 0,5 ... 2,5 mm² flexible conductor
- · load circuit, electrical:
 - plain flexible conductor, min. 1 mm²: current carrying capacity max. 6 A
 - flexible conductor with terminal pin, crimped on gas tight, min. 1,5 mm²: current carrying capacity max. 10 A
 - all other conductors, min. 1,5 mm²: current carrying capacity max. 16 A

\triangle

WARNING

When looping through the L-conductor (connection blocks 1 and 2, 4 and 5, 7 and 8, 10 and 11, 13 and 14, 16 and 17, 19 and 20, 22 and 23) take care that the maximum connection current of 20 A (as governed by the maximum permissible printed conductor load) is not exceeded!

- bus line
 - pressure contacts on data rail
 - screwless bus connection block 0,6...0,8 mm Ø single core remove approx. 5mm of isolation

Physical specifications

- · housing: plastic
- N-system DIN-rail mounted device, width: 8 SUs (1 SU = 18 mm)
- weight: approx. 560 g
- fire load: approx. 6080 kJ \pm 10 %
- installation: rapid mounting on DIN EN 60715-TH35-7,5 rail

Electrical safety

- degree of pollution (according to IEC 60664-1): 2
- protection (according to EN 60529): IP 20
- overvoltage class (according to IEC 60664-1): III
- bus: safety extra low voltage SELV DC 24 V
- relay with µ-contact
- device complies with:
 EN 50090-2-2 and EN 60669-2-1

Reliability

• rate of failure: 766 fit at 40 °C

Electromagnetic compatibility

complies with

EN 50081-1, EN 50082-2 and EN 50090-2-2

Environmental specifications

- climatic conditions: EN 50090-2-2
- ambient temperature operating: 5 ... + 45 °C
- ambient temperature non-op.: 25 ... + 70 ° C
- relative humidity (non-condensing): 5 % to 93 %

Certification

EIB certificate

CE norm

complies with the EMC regulations (residential and functional buildings), and low voltage regulations.

Load Switch N 512 5WG1 512-1AB01 8 x 230 V AC / 16 A

Operator Elements




Figure 1: Location of the display and operator elements

- A1 LED for indicating normal operating mode (LED off) and addressing mode (LED on); upon receiving the physical address the device automatically returns to normal operating mode
- A2 learning button for switching between normal operating mode and addressing mode for receiving the physical address
- A3 screw blocks for connecting load circuits
- A4 screwless bus connection block
- A5 Slide switch for manual operation and for displaying the switching position.
 - Slide in upper position: relay contact closed Slide in lower position: relay contact open

Mounting and Wiring

General description

The N-system DIN-rail device (8 SUs) can be installed to N-system distribution boards, surface or flush mounted, or to any DIN-rail EN 50022-35 x 7,5 available that has a data rail installed.

The connection to the bus line is established by clicking the device onto the DIN-rail (with a data rail installed). Take care that the type plates of all devices on a DIN-rail can be read in the same direction, guaranteeing the devices are polarised correctly.

If the connection is established via bus connection block (data rail not installed) the data rail connection system has to be covered with the enclosed insulation hood after removing the guiding hood e.g. with a screw driver to guarantee a sufficient insulation from the DIN rail.

If the load switch N 512 is installed the conventional adapter is not necessary (also for other DIN-rail devices). The bus voltage is downloaded from the bus connection block to the data rail.

Mounting DIN-rail devices (Figure 2)

- Slide the device (B1) onto the DIN-rail (B2) and
- swivel back the device until the slide clicks into place audibly.

Dismounting DIN-rail devices (Figure 2)

- Remove all connected wires.
- press down the two slides (C3) with a screw-driver and
- swivel the device (C1) from the DIN-rail (C2).




Figure 2: Mounting and dismounting a DIN-rail device

Removing the guiding top (Figure 3)

- The guiding top (D3) surrounds the contact system (D2) on the back side of the load switch N 512 (D1).
- Insert the screw driver between the DIN-rail device (D1) and the guiding hood (D3) and remove the guiding hood.

Inserting the insulation top (Figure 3)

- Put the insulation top (D4) onto the contact system and click it into place by a slight pressure.




Figure 3: Mounting and dismounting a DIN-rail device

Slipping off bus connection blocks (Figure 4)

 The bus connection block (E1) is situated on the top of the N 512 (E2).

Technical Product Information

April 2003

Load Switch N 512 5WG1 512-1AB01 8 x 230 V AC / 16 A

- The bus connection block (E1) consists of two components (E1.1 and E1.2) with four terminal contacts each. Take care not to damage the two test sockets (E1.3) by accidentally connecting them to the bus cable or with the screw-driver (e.g. when attempting to unplug the bus connection block).
- Carefully put the screw-driver to the wire-inserting slit of the bus connection block's grey component and pull the bus connection block (E1) from the load switch N 512 (E2).

Note:

Don't try to remove the bus connection block from the bottom side! There is a risk of shorting-out the device!

Slipping on bus connection blocks (Figure 4)

- Slip the bus connection block onto the guide slot and
- press the bus connection block (E1) down to the stop.

Connecting bus cables (Figure 4)

- The bus connection block (E1) can be used with single core conductors Ø 0,6 ... 0,8 mm.
- Remove approx. 5 mm of insulation from the conductor (E1.4) and plug it into the bus connection block (E1) (red = +, black = -).

Disconnecting bus cables (Figure 4)

 Unplug the bus connection block (E1) and remove the bus cable conductor (E1.4) while simultaneously wiggling it.




Figure 4: Connecting and disconnecting bus wires

Connecting load circuits (Figure 5)

- Remove approx. 8 to 9 mm of insulation from the wire (F1.1) and plug it into the terminal (F1) and tighten the screws (F1.2)
- cross sections load circuit, physical: strip insulation for 8 ... 9 mm permissible conductor types/cross sections:
 - 0,5 ... 4 mm² single core
 0,5 ... 2,5 mm² flexible conductor

, ,

Disconnect load circuits (Figure 5)

- Release the screw (G1.2) and remove the wire (G1.1) from the terminal (G1).





Figure 5: Connecting and disconnecting load circuits

Important hint:

The manual operation of the sliding switches is only designated as an emergency operation. There is no telegram downloaded to the bus and the changed position is not recognised by the bus controller. In case of bus voltage failure/recurrence even the switching conditions of manually controlled relays resume the condition set in parameter list.

Dimension Diagram

Dimensions in mm



Technical Manual

Technical Product Information

April 2003

Load Switch N 512 5WG1 512-1AB01 8 x 230 V AC / 16 A

1 Spacer Unit (SU) = 18mm

General Notes

- Any faulty devices should be returned to the local Siemens office.
- If you have further questions about the product, please contact our Technical Support:
 - ★ +49 (0) 180 50 50-222
 - 49 (0) 180 50 50-223
 - □ adsupport@siemens.com