

GAMMA instabus

Technical Product-Information

April 2021


Power Supply Unit N 125/02
Power Supply Unit N 125/12
Power Supply Unit N 125/22

5WG1125-1AB02 5WG1125-1AB12 5WG1125-1AB22

Product – and Applications Description







The power supply unit provides the system power necessary for KNX. The connection to the bus line is established via the bus connection block located on the front side.

The integrated choke prevents the data telegrams from short-circuiting on the bus line. When the built-in reset switch is operated (operation > 20s), the bus devices are returned to their initial state.

For each bus line, at least one power supply unit is needed. Up to two power supply units may be attached to a single bus line. A second unit is not required unless the supply voltage at a bus device is less than 21 V.

Note: If two power supply units N 125/_2 are operated in parallel on one bus line and if the overload LED is lit on one or both power supplies, then the bus configuration has to be changed until the overload display disappears.

Two devices of the same type can be connected directly in parallel to double the current required for a line. No minimum bus cable length is required between the two KNX power supplies.

When more than 30 bus devices are installed in short bus cable distance (e.g. 10 m), e.g. in distribution boards, the power supply unit should be arranged near these bus devices. The distance between power supply unit and any of its bus devices must not exceed 350 m.

The power supply unit has a voltage and current regulation and is therefore short-circuit proof. Short power failures can be bridged with a backup interval of approximately 200 ms.


To ensure an uninterrupted power supply a separate circuit with safety separation should be used for the power supply unit power supply line.

The power supply units can supply DC 24 V power from an additional pair of terminals (yellow/white). This DC 24 V output voltage can be used to power e.g. an additional line via a separate choke N 120.

The power supply units N $125I_2$ can be powered by AC 120...230 V or by DC 220 V.

More information www.siemens.com/gamma-td

Example of Operation



1/4

Update: http://www.siemens.com/gamma-td

Power Supply Unit N 125/02	5WG1125-1AB02
Power Supply Unit N 125/12	5WG1125-1AB12
Power Supply Unit N 125/22	5WG1125-1AB22

Installation Instructions

• The device may be used for permanent interior installations in dry locations within distribution boards or small casings with DIN rail EN 60715-TH35.



WARNUNG

- The device may be built into distribution boards (230/400 V) together only with appropriate VDE-devices.
- The device must be mounted and commissioned by an authorised electrician.
- A safety disconnection of the device must be possible.
- The prevailing safety rules must be heeded.
- The device must not be opened.
- For planning and construction of electric installations, the relevant guidelines, regulations and standards of the respective country are to be considered.

Technical Data Input voltage

• rated voltage: AC 120-230 V, 50...60 Hz

DC 220 V

• permissible range: AC 102...253V, DC 176...270 V

Rated power intake

approx. 24 VA

Output voltage

• rated voltage: DC 24 V

• safety extra low voltage (SELV)

• permissible range: DC 21...30 V

Output current

rated current 160 mA (N 125/02),

320 mA (N 125/12), 640 mA (N 125/22)

• short-circuit current:

limited to

1.0 A (N 125/02, N 125/12),

1.5 A (N 125/22)

Backup interval

on input voltage failure: approx. 200 ms at rated current

Operator elements

slide switch: for resetting the bus devices connected to the line (operation > 20 s)

Display elements

- 1 red LED: for indicating a voltage interruption on operating the slide switch in RESET-position
- 1 green LED: for indicating normal operation
- 1 red LED: for indicating a shorted-out bus line or device over-load

Connections

- mains connection, screwless plug-in terminals: strip insulation for 10...11 mm permissible conductor types/cross sections:

 - 0.5...3.3 mm² (AWG 12) single core
 0.5...1.5 mm² plain flexible conductor
 - 0.5...3.3 mm² (AWG 12) stranded conductor
 - 0.5...3.3 mm² (AWG 12) flexible conductor with terminal pin, crimped on gas tight

Technical Product-Information

April 2021

Power Supply Unit N 125/02	5WG1125-1AB02
Power Supply Unit N 125/12	5WG1125-1AB12
Power Supply Unit N 125/22	5WG1125-1AB22

- bus line:
 - screwless extra low voltage terminal (red/black) \varnothing 0.6...0.8 mm
- output voltage (no choke): screwless extra low voltage terminal (yellow/white)
 Ø 0.6...0.8 mm

Physical specifications

- housing: plastic
- dimensions: N-system DIN-rail mounted device, width: 4 SU (1 SU = 18 mm)
- Fire load: approx. 3700 kJ
- weight: approx. 260 g
- installation: rapid mounting on DIN rail according to EN 60715-TH35

Electrical safety

- degree of pollution (according to IEC 60664-1): 2
- protection (according to EN 60529): IP 20
- Overvoltage category (according to IEC 60664-1): III
- bus: safety extra low voltage SELV DC 24 V
- device complies with EN 50 491-3, EN 61558-2-6 and EN 61558-2-16

Electromagnetic compatibility

complies with EN 50491-5-1, -5-2, -5-3

Environmental specifications

- climatic conditions: EN 50090-2-2
- ambient temperature operating: 5...+ 45 °C
- storage temperature: 25...+ 70 ° C
- relative humidity (non-condensing): 5 % to 93 %

Reliability

Failure rate: 1178 fit at 40°C


Markings

EIB KNX certified

CE mark

complies with the EMC regulations (residential and functional buildings), and low voltage regulations

Location and Function of the Display and Operating Elements



- A1 extra low-voltage bus terminals (red/black)
- A2 reset switch
- A3 extra low-voltage terminals (yellow/white)
- A4 type plate
- A5 red LED for indicating that A2 is in reset position; the power supply unit N 125/ 2 does not supply power
- A6 green LED for indicating normal operation of the power supply unit N 125/ 2
- A7 red LED for indicating a shorted-out bus line or a device over-load
- A8 screwless plug-in terminals for connecting the mains (mains terminals)
- A9 screwless plug-in terminal for ground (protective earth terminal)

Update: http://www.siemens.com/gamma-td

Power Supply Unit N 125/02	5WG1125-1AB02
Power Supply Unit N 125/12	5WG1125-1AB12
Power Supply Unit N 125/22	5WG1125-1AB22

Mounting and Wiring

Connecting mains (figure 3)

- The mains are connected via screwless plug-in terminals (E1).
- Remove approx. 10...11 mm of insulation from the wire (E2) and plug it into the terminal (E1).

Disconnecting the mains (figure 3)

- Press the terminal lock (E3) of the terminal (E1) with a screwdriver and
- remove the wire (E2) from the terminal (E1).




Figure 3: Connecting and disconnecting wires

Slipping on of the safety extra low voltage block

- slip the connection block onto the guide slot and
- press the connection block down to the stop

Connecting the safety extra low voltage block (figure 4)

- The connection block (F2) can be used with single core conductors Ø 0.6...0.8 mm.
- The connection block (F2) consists of a red (yellow) connector (F2.1) and a black (white) connector (F2.2). Each connector can take up to four wires with single core conductors Ø 0.6...0.8 mm.
- Remove approx. 5 mm of insulation from the conductor (F2.4) and plug it into the connection block (F2) (red = +, black = -).

<u>Disconnecting the safety extra low voltage block</u> (figure 4)

 Unplug the connection block (F2) and remove the bus cable conductor (F2.4) while simultaneously wiggling it.





Figure 4: Connecting and disconnecting safety extra low voltage block

Dimension Diagram

Dimensions in mm



b = 4 SU

1 Standard unit (SU) = 18 mm

General Notes

- The operating instructions must be handed over to the client.
- Any faulty device is to be sent together with a return delivery note of the local Siemens office.
- For any technical questions, please consult:

+49 (911) 895-7222

♣ +49 (911) 895-7223

□ support.automation@siemens.com
 www.siemens.com/automation/support-request

Update: http://www.siemens.com/gamma-td